

The P163BAA can be supplied with any of our range of Bed or Chair Vacation sensors or a Floor Mat to assist in fall prevention, the detection of wandering or collapse.

It can also be used with any switch device to create a two level alarm trigger




The P163 provides a general alarm detection unit compatible with a range of switches and sensors, and the functionality is readily adapted for a many conditions.

The alarm is transmitted to a pager or telephone dialler using secure high integrity radio, with a range of over 450m outdoors.


The unit is battery powered (2*AA) with a rechargeable option using a 9-12v mains adapter.

Typical battery life is over 1 year and a low battery warning is radioed to the pager

Additionally the unit has an integral Call Button and can also be set to alarm on sustained high or low ambient temperature (eg for Hypothermia or fire detection).



The P163BBA is compatible with our range of Moisture Detection sheets for situations involving incontinence or vomiting



The P163AC has a dual function Call Button operated by simply lying a hand, foot or any item on top of the unit. The dual level triggers a low urgency ASSIST alarm on a short contact but escalates this to emergency on a long contact (5 seconds)



This is just one of the many distress sensing products available, which all communicate the alarm condition to the P137 pager to provide carers with extended vigilance